

**Linishing belt aluminium oxide (A) KK711X, 100×950 mm, Grit: 60****Order data**

Order number	558030 60
GTIN	4018875157473
Item class	56V

Description**Version:**

Universal linishing belt with **Aluminium Oxide(A)**. The grinding medium underlay is optimally designed to the grit and type of linishing belt.

Robust X-fabric for **high material removal rate** on stationary grinding machines.

Application:

For universal use on all popular materials: **steel**, non-ferrous metals, cast iron, **aluminium alloys**, **wood**.

Note:

Other grit sizes, qualities, and dimensions are available on request in line with the manufacturer's minimum order quantities. Unless specified otherwise on the order, belts will be supplied with standard joints. See No. 568526ff for spare linishing belts for burnishing machines.

Technical description

Grit	60
Series	KK711X
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	100 mm
Linishing belt length	950 mm
Product name attribute	100×950 mm
Type of product	Linishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable	35-40 m/s	
Steel < 900 N/mm ²	suitable	32-38 m/s	P
Steel < 1400 N/mm ²	suitable only under restricted conditions	20-25 m/s	P
Steel < 55 HRC	suitable only under restricted conditions	32-38 m/s	H
INOX	suitable only under restricted conditions	18-30 m/s	
Ti	suitable only under restricted conditions	10-20 m/s	
GG(G)	suitable only under restricted conditions	30-45 m/s	K
CuZn	suitable	35-45 m/s	N
Plastic, GRP	suitable	10-30 m/s	
Wood	suitable	23-26 m/s	
dry	suitable		