




Multi-purpose hand file with handle, special cut, Length without tang: 300mm



Order data

Order number	515000 300
GTIN	4009215074697
Item class	56B

Description

Version:

The blanks are forged and ground; manufactured with an exact cut of even density and depth using special machines. These **non-convex files** have tooth profiles appropriate to each grade of file.

Hand files with corner radius profile teeth and wide chip breakers for easy, low force filing and very high metal removal rates no clogging of the teeth good filings clearance.

Flat faces with special cut, one side with filings breaker groove for highest removal rate. File with square end. Rear face with continuous cut for particularly fine finishing. File with plain end. Plastic handle with hanging hole.

Application:

The **quality file** for workshop use with long tool life and high removal rate.

Technical description

Cross section	30×6,5 mm
Length without tang	300 mm
Type of product	Multi-purpose file

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		

Steel < 900 N/mm ²	suitable
Steel < 1400 N/mm ²	suitable only under restricted conditions
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable only under restricted conditions
INOX	suitable only under restricted conditions
GG(G)	suitable
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable

Accessories

File brush Bristle length L3× width L1 80X20 mm	576000 80X20
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
File brush Bristle length L3× width L1 100X25 mm	576000 100X25