

**Base cabinet for measuring microscopes, width×depth: 1500X700 mm****Order data**

Order number	491914 1500X700
GTIN	4045197488633
Item class	41M

Description**Version:**

Body of welded sheet steel, with bench top of Beolin, curved at one end; edges veneered with 3 mm thick graphite. With handy sheet steel storage shelf. Incorporating the GARANT locking system.

Suitable for :

GARANT video measuring microscope with measuring area max. X = 200 / Y = 100.

Components:

Drawer front height (left): 60; 300; 300 mm

Colour:

Body white aluminium RAL 9006, drawers steel blue RAL 5011.

Cylinder lock: modular barrel

Drawer usable width: 490 mm

Drawer usable depth: 520 mm

Load capacity, distributed: 1000 kg

Weight: 124 kg

Technical description

Load capacity, distributed	1000 kg
----------------------------	---------

Drawer usable width	490 mm
Electronic locking system can be retrofitted	yes
Weight	124 kg
Drawer usable depth	520 mm
Number of drawers	3
Workbench height	840 mm
Drawer/pull-out shelf load capacity	100 kg
Worktop thickness	50 mm
Drawer runner extension	90 %
Hoffmann perforated panel grid interval	9×9
Cylinder lock	modular barrel