




**Set of engineer's files, 5 pieces, in a tool roll Cut 2, with wooden handle,
Length without tang: 200mm**



Order data

Order number	517240 200
GTIN	4009215169928
Item class	56B

Description

Version:

The blanks are forged and ground; manufactured with an exact cut of even density and depth using special machines. These **non-convex files** have tooth profiles appropriate to each grade of file.

To protect the files, the set is arranged in a **strong transparent roll-up nylon wallet**.

Protected files cannot be contaminated and the cut is protected against damage; this ensures a consistently high removal rate, smooth file surfaces, and an extended working life.

With hardwood file handle.

2nd cut = Cut 2.

Application:

Quality file for workshop use with long tool life and high removal rate.

Supplied with:

5-piece set of files with one each **flat, 3-square, square, half-round and round file**.

Technical description

Length without tang	200 mm
Cut	2
Standard	DIN 7261

Type of product

Engineer's file

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		

Accessories

File brush Bristle length L3× width L1 80X20 mm	576000 80X20
File brush Bristle length L3× width L1 100X25 mm	576000 100X25
File brush Bristle length L3× width L1 115X40 mm	576000 115X40