



## Set of engineer's files, 5 pieces, in a tool roll Cut 3, Length without tang: 300mm



### Order data

Order number	517300 300
GTIN	4009215074819
Item class	56B

### Description

#### Version:

The blanks are forged and ground; manufactured with an exact cut of even density and depth using special machines. These **non-convex files** have tooth profiles appropriate to each grade of file.

To protect the files, the set is arranged in a **strong transparent roll-up nylon wallet**.

Protected files cannot be contaminated and the cut is protected against damage; this ensures a consistently high removal rate, smooth file surfaces, and an extended working life.

With impact resistant plastic handles.

**Smooth** = Cut 3.

#### Application:

**Quality file** for workshop use with long tool life and high removal rate.

#### Supplied with:

**5-piece** set of files with one each **flat, 3-square, square, half-round and round file**.

### Technical description

Length without tang	300 mm
Cut	3
Standard	DIN 7261

Type of product

Engineer's file

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable only under restricted conditions		
INOX	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		

## Accessories

File brush Bristle length L3× width L1 100X25 mm	576000 100X25
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
File brush Bristle length L3× width L1 80X20 mm	576000 80X20