



## LED cold light source, Type: F1



### Order data

Order number	492242 F1
GTIN	2050002047051
Item class	49K

### Description

#### Version:

Very bright dimmable cold light source with long-life (> 30,000 h) and energy-saving LED technology (5800 K). Sturdy metal casing, can be stacked as a stable assembly. ESD socket for dissipating static electrical charges. Extremely high light densities at the illuminated area. Passive cooling, silent and vibration-free.

#### Supplied with:

LED cold light source, double swan neck fibre optic cable (Ø 4.5 mm, length 550 mm) with integral focussing lenses. Including international power supply unit (100 – 240 V).

#### Optional extras:

Halogen filter No. 492244 size FILTER, foot switch No. 492244 size SWITCH and cross section converter No. 492244 size LINE.

#### Note:

Further fibre optic cables, gap ring light sources, colour filters and other accessories available on request.

### Technical description

Weight	0.5 kg
Power supply	Mains operated
comparable light output to a halogen bulb	100 W

Power consumption	22 W
Colour temperature	5800 K
Overall width	110 mm
Overall height	175 mm
Overall length	196 mm
Intensity of illumination	350 lm
Type of product	Lighting unit for measuring tool

---

## Accessories

Accessories for LED cold light sources Type SWITCH	492244 SWITCH
Accessories for LED cold light sources Type LINE	492244 LINE
Accessories for LED cold light sources Type FILTER	492244 FILTER