



LED cold light source, Type: F3000



Order data

| | |
|--------------|---------------|
| Order number | 492242 F3000 |
| GTIN | 4045197578235 |
| Item class | 49K |

Description

Version:

Very bright dimmable cold light source with long-life (> 30,000 h) and energy-saving LED technology (5800 K). Sturdy metal casing, can be stacked as a stable assembly. ESD socket for dissipating static electrical charges. Extremely high light densities at the illuminated area. Remotely controlled with a foot switch or USB, extremely quiet fan. Shutter functionality. Can be used in vertical orientation.

Optional halogen filter simulates halogen light 3500 K.

Supplied with:

LED cold light source, double swan neck fibre optic cable (Ø 4.5 mm, length 550 mm) with integral focussing lenses. With EU mains cable.

Optional extras:

Halogen filter No. 492244 size FILTER, foot switch No. 492244 size SWITCH and cross section converter No. 492244 size LINE.

Note:

Further fibre optic cables, gap ring light sources, colour filters and other accessories available on request.

Technical description

| | |
|--------------|----------------|
| Weight | 3.8 kg |
| Power supply | Mains operated |

| | |
|---|----------------------------------|
| Power consumption | 65 W |
| comparable light output to a halogen bulb | > 150 W |
| Colour temperature | 5800 K |
| Overall width | 170 mm |
| Overall height | 98 mm |
| Overall length | 196 mm |
| Intensity of illumination | 640 lm |
| Type of product | Lighting unit for measuring tool |

Accessories

| | |
|--|---------------|
| Accessories for LED cold light sources Type FILTER | 492244 FILTER |
| Accessories for LED cold light sources Type LINE | 492244 LINE |
| Accessories for LED cold light sources Type SWITCH | 492244 SWITCH |