

**Video endoscope with probe flexible, Ø 5.5 mm, Probe length: 2000mm****Order data**

Order number	492925 2000
GTIN	4045197511812
Item class	42L

Description**Version:**

Base unit with 3.5 inch LCD display. Zoom mode (1.5×), image and video data can be saved on an SD memory card. USB and AV ports for data transmission. Integral rechargeable lithium-ion battery (3.7 V).

Supplied with:

Sturdy watertight and dust-tight transport case. SD memory card, power supply unit (AC 100 – 240 V / 50 – 60 Hz) No. 492958, USB data cable, AV cable, cleaning set, lithium-ion battery No. 492926.

1 probe No. 492938 size 2000 (IP67), screw-on probe mirror No. 492950 (70°, 90°, 110°) and magnet.

Technical description

Length	207 mm
Probe length	2000 mm
Weight	0.558 kg
Width	118 mm

depth of focus when focussed	16 – 60 mm
Display resolution	320×240 px
Height	38 mm
Camera resolution	640×480 px
Recording format	JPEG / AVI (30 fps)
Operating temperature	0 - 50 °C
Power supply	Mains operated
Probe Ø	5.5 mm
Type of product	Endoscope

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/492925-2000>