

**Video endoscope with probe flexible, Ø 5.5 mm, Probe length: 2000 mm****Order data**

Order number	492925 2000
GTIN	4045197511812
Item class	42L

Description**Version:**

Base unit with 3.5 inch LCD display. Zoom mode (1.5×), image and video data can be saved on an SD memory card. USB and AV ports for data transmission. Integral rechargeable lithium-ion battery (3.7 V).

Supplied with:

Sturdy watertight and dust-tight transport case. SD memory card, power supply unit (AC 100 – 240 V / 50 – 60 Hz) No. 492958, USB data cable, AV cable, cleaning set, lithium-ion battery No. 492926.

1 probe No. 492938 size 2000 (IP67), screw-on probe mirror No. 492950 (70°, 90°, 110°) and magnet.

Recording format: JPEG / AVI (30 fps)

Camera resolution: 640×480 px

Display resolution: 320×240 px

depth of focus when focussed: 16 – 60 mm

Operating temperature: 0 - 50 °C

Weight: 0.558 kg

Technical description

Length	207 mm
Probe length	2000 mm
Weight	0.558 kg
Width	118 mm
depth of focus when focussed	16 – 60 mm
Display resolution	320×240 px
Height	38 mm
Camera resolution	640×480 px
Recording format	JPEG / AVI (30 fps)
Operating temperature	0 - 50 °C
Power supply	Mains operated
Probe Ø	5.5 mm
Type of product	Endoscope

Accessories

Mains adapter for endoscope	492958
Endoscope probe, flexible Probe length 2000 mm	492940 2000
Endoscope probe, flexible Probe length 2000 mm	492938 2000
Endoscope probe, semi-rigid Probe length 1000 mm	492936 1000
Endoscope probe, elbow bend, flexible Probe length 1000 mm	492942 1000
Lithium ion battery	492926
Endoscope probe, semi-rigid Probe length 1000 mm	492934 1000