


Garant**Flap wheel (CER), 120 grit, Head Ø×head width: 50X20mm****Order data**

Order number	554170 50X20
GTIN	4045197882844
Item class	51E

Description**Version:**

Flap strips bonded on to the shank of the tool.
Abrasive strips covered with **ceramic grit (CER)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Technical description

Head Ø	50 mm
Shank Ø	6 mm
maximum speed	15300 min ⁻¹
Grit	120
Head width	20 mm
recommended speed	9000 min ⁻¹
Grinding media	Ceramic grit (CER)

Grinding medium code	Ceramic
Product name attribute	120 grit
Type of product	Flap wheel

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable only under restricted conditions		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
dry	suitable		