

RENISHAW**Probe extension, Length: 50mm****Order data**

| | |
|--------------|---------------|
| Order number | 494202 50 |
| GTIN | 2050000965562 |
| Item class | 49D |

Description**Version:**

Extension – M8 to M8.

Suitable for:

Probe holder No. 494210 TP20 and No. 499205 TP200.

Note:

Probe extensions in other sizes and shank types available on request.

Technical description

| | |
|-------------------------|-----------|
| Length | 50 mm |
| Shank $\varnothing D_1$ | 13 mm |
| Weight | 27 g |
| Shank $\varnothing D_2$ | 13 mm |
| Material | Aluminium |
| Type of product | Extension |

Accessories

| | |
|--|-----------|
| Probe module TP20 Type EF | 494212 EF |
| Stylus, cylindrical Cylinder $\varnothing D$ 2R mm | 494230 2R |

| | |
|---|---------------|
| Probe module TP20 Type EM1SF | 494212 EM1SF |
| Stylus, ruby ballLength 10/11 mm Contact point Ø D 1 mm | 494220 1 |
| Probe module TP20 Type SF | 494212 SF |
| Probe module TP20 Type 6W | 494212 6W |
| Probe module TP20 Type EM2STD | 494212 EM2STD |
| Probe module TP20 Type LF | 494212 LF |
| Stylus, ruby ballLength 20 mm Contact point Ø D 1,5 mm | 494222 1,5 |
| Stylus, ruby ballLength 40 mm Contact point Ø D 4 mm | 494224 4 |
| Probe module TP20 Type MF | 494212 MF |