

**RENISHAW****Stylus, ruby ball Length 10/11 mm, Contact point Ø D: 3mm****Order data**

Order number	494220 3
GTIN	2050000973406
Item class	49F

**Description****Version:**

Ruby-tipped probe with M2 connection thread

**Note:**

Further styli with other sizes and shank types available on request.

**Technical description**

Shank Ø S	1.5 mm
effective working length	7 mm
Material of shank	Steel
Weight	0.4 g
Contact point Ø D	3 mm
Length L	10 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

**Accessories**

Stylus extension Length 20 mm	494214 20
-------------------------------	-----------

Adaptor Type M3/M2	494218 M3/M2
Stylus extension Length 10 mm	494214 10
Stylus extension Length 40 mm	494214 40
Stylus extension Length 30 mm	494214 30
5-way stylus centre M2 Type M2/5	494219 M2/5
Stylus cleaning kit	494240