



Zirconium Aluminium Oxide (ZA) linishing belt GRIT R, 75×2000 mm, Grit: 36



Order data

| | |
|--------------|---------------|
| Order number | 558453 36 |
| GTIN | 4014586278506 |
| Item class | 56Z |

Description

Version:

Top quality linishing belt, **extra heavy-duty polyester fabric** with synthetic resin bonding, Zirconium Aluminium Oxide (**ZA**) with active upper layer bonding (cool cut).

Application:

For GRIT belt linishing machines series GX, GIS, GI.

Technical description

| | |
|---|--------------------------------|
| Grit | 36 |
| Grinding media | Zirconium aluminium oxide (ZA) |
| Grinding medium code | ZA |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Linishing belt width | 75 mm |
| Linishing belt length | 2000 mm |
| Product name attribute | 75×2000 mm |

Type of product

Linishing belt

User data

| | Suitability | V_c | ISO code |
|--------------------------------|--------------------|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | 32-38 m/s | P |
| Steel < 1400 N/mm ² | suitable | 20-25 m/s | P |
| Steel < 55 HRC | suitable | 32-38 m/s | H |
| Steel < 60 HRC | suitable | 25-30 m/s | H |
| Steel < 67 HRC | suitable | 20-25 m/s | H |
| INOX | suitable | 18-30 m/s | |
| Ti | suitable | 10-20 m/s | |
| GG(G) | suitable | 30-45 m/s | K |
| Wood | suitable | 23-26 m/s | |
| dry | suitable | | |