



VALTITAN precision half-round file, Length without tang mm / Swiss cut: 200/0



Order data

Order number	525050 200/0
GTIN	613548062579
Item class	53B

Description

Version:

VALTITAN high performance precision files with extremely high wear resistance due to surface hardness of **1200 HV**. The special tooth profile prevents the file becoming clogged. Maximum metal removal rate and tool life. Virtually non-rusting, therefore suitable for use in highly corrosive environments. Leaves no corrosion-susceptible residues.

Cuts on all faces; tapers to a point.

Technical description

Cross section	21.1×6.3 mm
Length without tang	200 mm
equivalent to German cut	2
Type of product	Precision file

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		

Steel < 60 HRC	suitable
Steel < 67 HRC	suitable
INOX	suitable
Ti	suitable
GG(G)	suitable
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable
Uni	suitable

Accessories

2-component ergonomic file handle Overall length 120 mm	519600 120
Plastic file handle Overall length 110 mm	519550 110
Plastic file handle Overall length 100 mm	519510 100
File brush Bristle length L3× width L1 80X20 mm	576000 80X20
File brush Bristle length L3× width L1 100X25 mm	576000 100X25
File brush Bristle length L3× width L1 115X40 mm	576000 115X40
Plastic file handle Overall length 110 mm	519510 110
2-component ergonomic file handle Overall length 110 mm	519600 110
Hardwood file handle Overall length 120 mm	519400 120