

## Test pin set in a wooden box Tolerance class 1, Type: 91



### Order data

Order number	483800 91
GTIN	2050001046710
Item class	48A

### Description

#### Version:

Of high quality gauge steel, hardened ( $60 \pm 2$  HRC) and tempered. The test pin sets are arranged in a wooden case for ease of location, with labelled holes (from 1.5 mm  $\varnothing$  the pins are also directly marked). Test pin length 40 mm up to  $\varnothing$  0.99 mm, 70 mm above that.

**Tolerance class 1:** Pin  $\varnothing \pm 0.001$  mm.

#### Application:

For work on jig boring machines or in jig and tool making, e. g. for measuring bore tolerances, for checking positions of bores, checking the spacing tolerances of two bores, gearwheel or thread dimensions as well as for angle and profile inspections etc.

### Technical description

Pitch	0.1 mm
Number of test pins	91
Nominal size range	1 - 10 mm
Standard	DIN 2269
Tolerance class	1
Hardness	$60 \pm 2$ HRC

Material	Gauge steel
Packaging	sturdy box
Calibration	S18
Type of product	Test pin

**Services**

DAkkS calibration Test pin set Set contents 91	020890 91
Calibration Test pin set Set contents 91	020880 91