



Habilis precision file Overall length 215 mm, SC 1 / GC 3, Type: 5



Order data

Order number	527070 5
GTIN	613548056271
Item class	53B

Description

Version:

Swiss precision files with highest shape accuracy, cut precision, removal rate, and tool life. Shapes similar to needle files, however with **strong, forged** square or hexagonal **tang** and strengthened cross section.

No file handle required.

Application:

Particularly suitable for tool and mould making due to tapered, slim shape. **Habilis precision files** allow **heavier working pressures** than needle files.

Technical description

Shape description	square
Cross section	6.0×6.0 mm
Overall length	215 mm
Swiss cut	1
equivalent to German cut	3
Product name attribute	SC 1 / GC 3
Type of product	Precision file

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		

Steel < 900 N/mm ²	suitable
Steel < 1400 N/mm ²	suitable
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable
Steel < 67 HRC	suitable
INOX	suitable
Ti	suitable only under restricted conditions
GG(G)	suitable
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable
Uni	suitable only under restricted conditions