

Test pin set in a wooden box Tolerance class 2, Type: 41



Order data

Order number	483810 41
GTIN	2050001046727
Item class	48A

Description

Version:

Of high quality gauge steel, hardened (60 ± 2 HRC) and tempered. The test pin sets are arranged in a wooden case for ease of location, with labelled holes (from 1.5 mm \varnothing the pins are also directly marked). Test pin length 40 mm up to \varnothing 0.99 mm, 70 mm above that.

Tolerance class 2: Pin $\varnothing \pm 0.002$ mm.

Application:

For work on jig boring machines or in jig and tool making, e. g. for measuring bore tolerances, for checking positions of bores, checking the spacing tolerances of two bores, gearwheel or thread dimensions as well as for angle and profile inspections etc.

Technical description

Number of test pins	41
Nominal size range	1 - 5 mm
Pitch	0.1 mm
Standard	DIN 2269
Tolerance class	2

Hardness	60 ±2 HRC
Material	Gauge steel
Packaging	sturdy box
Calibration	S18
Type of product	Test pin

Services

DAkkS calibrationTest pin set Set contents 41	020890 41
CalibrationTest pin set Set contents 41	020880 41