



Digital hardness tester Shore A, Type: A



Order data

Order number	495002 A
GTIN	2050001672032
Item class	49G

Description

Version:

Shore hardness testers for determining hardness to Shore A or D to DIN ISO 7619-1 (supersedes DIN 53505) and ASTM D 2240. Sturdy, handy aluminium casing.

High-contrast bright LED graphical display. Memory for 100 measurement values with date and time. USB interface for PC and charger.

Application:

Shore A: Soft rubber, elastomers, natural rubber products, cast resin, leather, neoprene rubber, polyester, plasticised PVC.

Optional extras:

Test stand No. 495016. Test blocks for checking on request.

Software for generating test certificates, statistics, and graphics available on request.

Calibration: P1

Technical description

Manufacturer's designation	30-200
Power supply	Rechargeable battery-powered
Number of rechargeable batteries contained	1

Type of rechargeable battery	Lithium-ion
Test procedure	Shore A
Interface	USB interface
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Calibration	P1
Type of product	Hardness tester

Services

Calibration Shore A+D hardness tester	014700
DAkkS calibration Shore A+D hardness tester Type	017440
Calibration Shore A+D hardness tester Type H	029000 H
DAkkS calibration Shore A+D hardness tester Type H	029010 H

Accessories

Test stand	495016
------------	--------