



Analogue hardness tester Shore A, Type: A



Order data

Order number	495003 A
GTIN	2050001659620
Item class	49G

Description

Version:

Shore hardness testers for determining hardness to Shore A or D to DIN ISO 7619-1 (supersedes DIN 53505) and ASTM D 2240. Sturdy, handy aluminium casing.

Application:

Shore A: Soft rubber, elastomers, natural rubber products, cast resin, leather, neoprene rubber, polyester, plasticised PVC.

Optional extras:

Test stand No. 495016. Test blocks for checking on request.

Calibration: P1

Technical description

Manufacturer's designation	30-100
Test procedure	Shore A
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Calibration	P1

Type of product	Hardness tester
-----------------	-----------------

Services

Calibration Shore A+D hardness tester	014700
---------------------------------------	--------

DAkkS calibration Shore A+D hardness tester Type	017440
--	--------

Calibration Shore A+D hardness tester Type H	029000 H
--	----------

DAkkS calibration Shore A+D hardness tester Type H	029010 H
--	----------

Accessories

Test stand	495016
------------	--------