

RENISHAW**Stylus, ruby ball Length 20 mm, Contact point Ø D: 2mm****Order data**

Order number	494222 2
GTIN	2050000956782
Item class	49F

Description**Version:**

Ruby-tipped probe with M2 connection thread

Note:

Further styli with other sizes and shank types available on request.

Technical description

Contact point Ø D	2 mm
Weight	0.4 g
effective working length	14 mm
Shank Ø S	1.4 mm
Material of shank	Steel
Length L	20 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

Accessories

Stylus extension Length 20 mm	494214 20
-------------------------------	-----------

Stylus extension Length 10 mm	494214 10
Adaptor Type M3/M2	494218 M3/M2
Stylus extension Length 40 mm	494214 40
5-way stylus centre M2 Type M2/5	494219 M2/5
Stylus extension Length 30 mm	494214 30
Stylus cleaning kit	494240