

RENISHAW**Stylus, ruby ball Ceramic length 100 mm, Contact point Ø D: 5mm****Order data**

Order number	494236 5
GTIN	2050001740595
Item class	49F

Description**Version:**

Ceramic stylus with M4 connection thread for measuring machines and machine tools.

Note:

Further styli with other sizes and shank types available on request.

Technical description

Shank Ø S	3.8 mm
effective working length	83.5 mm
Material of shank	Ceramic
Contact point Ø D	5 mm
Weight	6.3 g
Length L	100 mm
Connection thread	M4
Material of point	Ruby
Type of product	Probes

Accessories

5-way stylus centre M2 Type M2/5	494219 M2/5
Adaptor Type M3/M2	494218 M3/M2

Stylus cleaning kit	494240
Stylus extension Length 20 mm	494214 20
Stylus extension Length 10 mm	494214 10
Stylus extension Length 40 mm	494214 40
Stylus extension Length 30 mm	494214 30