



Digital hardness tester Shore D, Type: D



Order data

Order number	495004 D
GTIN	2050001672049
Item class	49G

Description

Version:

Shore hardness testers for determining hardness to Shore A or D to DIN ISO 7619-1 (supersedes DIN 53505) and ASTM D 2240. Sturdy, handy aluminium casing.

High-contrast bright LED graphical display. Memory for 100 measurement values with date and time. USB interface for PC and charger.

Application:

Shore D: Hard rubber, hard plastics, Perspex, Formica, stiff thermoplastics, vinyl boards, polystyrene, pressure rollers.

Optional extras:

Test stand No. 495016. Test blocks for checking on request.

Supplementary weight No. 495018.

Software for generating test certificates, statistics, and graphics available on request.

Technical description

Manufacturer's designation	30-210
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion

Number of rechargeable batteries contained	1
Test procedure	Shore D
Interface	USB interface
Test certificate	Manufacturer's test certificate
Packaging	sturdy box
Calibration	P1
Type of product	Hardness tester

Services

CalibrationShore A+D hardness tester Type H	029000 H
DAkkS calibrationShore A+D hardness tester Type H	029010 H

Accessories

Test stand	495016
Supplementary weightfor Shore D	495018