

Test pin set in a wooden case Tolerance class 2, Type: 6-7



Order data

Order number	483830 6-7
GTIN	2050001048707
Item class	48A

Description

Version:

Of high quality gauge steel, hardened (60 ± 2 HRC) and tempered. The test pin sets are arranged in a wooden case for ease of location, with labelled holes (from 1.5 mm \varnothing the pins are also directly marked). Test pin length 40 mm up to \varnothing 0.99 mm, 70 mm above that.

Tolerance class 2: Pin $\varnothing \pm 0.002$ mm. 1 wooden box.

Application:

For work on jig boring machines or in jig and tool making, e. g. for measuring bore tolerances, for checking positions of bores, checking the spacing tolerances of two bores, gearwheel or thread dimensions as well as for angle and profile inspections etc.

Technical description

Nominal size range	6.01 - 7 mm
Pitch	0.01 mm
Number of test pins	100
Standard	DIN 2269
Tolerance class	2
Hardness	60 ± 2 HRC

Material	Gauge steel
Packaging	sturdy box
Calibration	S18
Type of product	Test pin

Services

CalibrationTest pin set Set contents 100	020880 100
DAkkS calibrationTest pin set Set contents 100	020890 100