

**Fleece finishing belt (A), 75×2000 mm, Grit equivalent: 280****Order data**

Order number	558488 280
GTIN	4045197526519
Item class	52E

Description**Version:**

Synthetic nylon non-woven fabric with synthetic resin bonded abrasive grit, long service life, **consistent surface finish, low heat generation.**

Application:

For rubbing down rough ground or brushed surfaces, for consistent and reproducible results. Also suitable for removing rust film, light soiling, and discolouration.

Technical description

Grit equivalent	280
Grit designation	very fine
Colour	blue
Version	A very fine
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

Linishing belt width	75 mm
Linishing belt length	2000 mm
Product name attribute	75×2000 mm
Type of product	Fleece linishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions	15-20 m/s	
Steel < 900 N/mm ²	suitable	10 m/s	P
Steel < 1400 N/mm ²	suitable	10 m/s	P
Steel < 55 HRC	suitable	10 m/s	H
Steel < 60 HRC	suitable	10 m/s	H
Steel < 67 HRC	suitable	10 m/s	H
INOX	suitable	10 m/s	
Ti	suitable	10 m/s	
GG(G)	suitable	10 m/s	K
CuZn	suitable	10 m/s	N
Plastic, GRP	suitable	10 m/s	
Wood	suitable	10 m/s	
Paint	suitable	10 m/s	
Uni	suitable	10 m/s	
dry	suitable		