

RENISHAW**Stylus, ruby ball Ceramic length 100 mm, Contact point Ø D: 6mm****Order data**

Order number	494236 6
GTIN	2050001740601
Item class	49F

Description**Version:**

Ceramic stylus with M4 connection thread for measuring machines and machine tools.

Note:

Further styli with other sizes and shank types available on request.

Technical description

Material of shank	Ceramic
Shank Ø S	4.5 mm
Weight	6.3 g
effective working length	88.5 mm
Contact point Ø D	6 mm
Length L	100 mm
Connection thread	M4
Material of point	Ruby
Type of product	Probes

Accessories

5-way stylus centre M2 Type M2/5	494219 M2/5
Stylus extension Length 40 mm	494214 40

Stylus cleaning kit	494240
Stylus extension Length 10 mm	494214 10
Adaptor Type M3/M2	494218 M3/M2
Stylus extension Length 20 mm	494214 20
Stylus extension Length 30 mm	494214 30