

RENISHAW**Stylus, ruby ball Length 20 mm, Contact point Ø D: 3mm****Order data**

| | |
|--------------|---------------|
| Order number | 494222 3 |
| GTIN | 2050000956799 |
| Item class | 49F |

Description**Version:**

Ruby-tipped probe with M2 connection thread

Note:

Further styli with other sizes and shank types available on request.

Technical description

| | |
|--------------------------|--------|
| Shank Ø S | 1.5 mm |
| Material of shank | Steel |
| effective working length | 17 mm |
| Weight | 0.5 g |
| Contact point Ø D | 3 mm |
| Length L | 20 mm |
| Connection thread | M2 |
| Material of point | Ruby |
| Type of product | Probes |

Accessories

| | |
|-------------------------------|-----------|
| Stylus extension Length 20 mm | 494214 20 |
|-------------------------------|-----------|

| | |
|----------------------------------|--------------|
| Stylus extension Length 10 mm | 494214 10 |
| Stylus extension Length 40 mm | 494214 40 |
| Stylus cleaning kit | 494240 |
| Stylus extension Length 30 mm | 494214 30 |
| 5-way stylus centre M2 Type M2/5 | 494219 M2/5 |
| Adaptor Type M3/M2 | 494218 M3/M2 |