



Analogue hardness tester Shore D, Type: D



Order data

Order number	495005 D
GTIN	2050001659637
Item class	49G

Description

Version:

Shore hardness testers for determining hardness to Shore A or D to DIN ISO 7619-1 (supersedes DIN 53505) and ASTM D 2240. Sturdy, handy aluminium casing.

Application:

Shore D: Hard rubber, hard plastics, Perspex, Formica, stiff thermoplastics, vinyl boards, polystyrene, pressure rollers.

Optional extras:

Test stand No. 495016. Test blocks for checking on request.

Supplementary weight No. 495018.

Calibration: P1

Technical description

Manufacturer's designation	30-110
Test procedure	Shore D
Test certificate	Manufacturer's test certificate
Packaging	sturdy box

Calibration	P1
Type of product	Hardness tester

Services

Calibration Shore A+D hardness tester	014700
DAkkS calibration Shore A+D hardness tester Type	017440
Calibration Shore A+D hardness tester Type H	029000 H
DAkkS calibration Shore A+D hardness tester Type H	029010 H

Accessories

Supplementary weight for Shore D	495018
----------------------------------	--------