

Single test pin Tolerance class 1, Type: 2



Order data

Order number	483900 2
GTIN	2050001048813
Item class	48A

Description

Version:

Of high quality gauge steel, hardened (60 ± 2 HRC) and tempered. Surface ground and lapped. From \varnothing 1.5 mm engraved with the size, 0.1 mm – 0.99 mm without a chamfer. From 1.0 mm one end chamfered.

Tolerance class 1: Pin $\varnothing \pm 0.001$ mm.

Application:

Degrease before use and grease after use.

Note:

When ordering, please additionally state the **desired \varnothing** , e.g. No. 483900 size 5 **10.08** or 483920 size 5 **10.082**.

Technical description

Pitch	0.01 mm
Gauging pin length	70 mm
Nominal size	1 - 2.99 mm
Calibration	L5
Standard	DIN 2269
Tolerance class	1
Hardness	60 ± 2 HRC
Material	Gauge steel
Type of product	Test pin

Services

DAkS calibration	Test pin maximum Ø 20	028260 20
Calibration	Test pin maximum Ø 20	028240 20