

RENISHAW**Stylus, ruby ball Length 20 mm, Contact point Ø D: 4mm****Order data**

Order number	494222 4
GTIN	2050000956805
Item class	49F

Description**Version:**

Ruby-tipped probe with M2 connection thread

Note:

Further styli with other sizes and shank types available on request.

Technical description

Shank Ø S	1.5 mm
Contact point Ø D	4 mm
Weight	0.6 g
Material of shank	Steel
effective working length	20 mm
Length L	20 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

Accessories

Stylus cleaning kit	494240
---------------------	--------

Stylus extension Length 40 mm	494214 40
Stylus extension Length 10 mm	494214 10
Stylus extension Length 20 mm	494214 20
Stylus extension Length 30 mm	494214 30
Adaptor Type M3/M2	494218 M3/M2
5-way stylus centre M2 Type M2/5	494219 M2/5