

**RENISHAW****Stylus, ruby ball Length 40 mm, Contact point Ø D: 2mm****Order data**

Order number	494224 2
GTIN	2050000973482
Item class	49F

**Description****Version:**

Ruby-tipped probe with M2 connection thread

**Note:**

Further styli with other sizes and shank types available on request.

**Technical description**

Shank Ø S	1.5 mm
Weight	1.29 g
Material of shank	Carbide
effective working length	32.5 mm
Contact point Ø D	2 mm
Length L	40 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

**Accessories**

Stylus extension Length 10 mm	494214 10
-------------------------------	-----------

Adaptor Type M3/M2	494218 M3/M2
Stylus extension Length 40 mm	494214 40
Stylus extension Length 20 mm	494214 20
5-way stylus centre M2 Type M2/5	494219 M2/5
Stylus cleaning kit	494240
Stylus extension Length 30 mm	494214 30