

3M**Fleece finishing belt (A) SC-BS, 10×330 mm, Grit equivalent: 100****Order data**

Order number	558492 100
GTIN	2050001694140
Item class	53M

Description**Version:**

Synthetic nylon non-woven fabric with synthetic resin bonded abrasive grit, long service life, **consistent surface finish, low heat generation.**

Flexible fleece belt for use on hand-held machines.

Application:

For rubbing down rough ground or brushed surfaces, for consistent and reproducible results. Also suitable for removing rust film, light soiling, and discolouration.

Technical description

Grit designation	coarse
Grit equivalent	100
Colour	brown
Version	A coarse
Series	SC-BS
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	10 mm
Linishing belt length	330 mm
Product name attribute	10×330 mm
Manufacturer's designation	SC-BS
Type of product	Fleece linishing belt

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions	15-20 m/s	
Steel < 900 N/mm ²	suitable	10 m/s	P
Steel < 1400 N/mm ²	suitable	10 m/s	P
Steel < 55 HRC	suitable	10 m/s	H
Steel < 60 HRC	suitable	10 m/s	H
Steel < 67 HRC	suitable	10 m/s	H
INOX	suitable	10 m/s	
Ti	suitable	10 m/s	
GG(G)	suitable	10 m/s	K
CuZn	suitable	10 m/s	N
Plastic, GRP	suitable	10 m/s	
Wood	suitable	10 m/s	
Paint	suitable	10 m/s	
Uni	suitable	10 m/s	
dry	suitable		