

RENISHAW**Stylus, ruby ball Length 40 mm, Contact point Ø D: 3mm****Order data**

Order number	494224 3
GTIN	2050000973499
Item class	49F

Description**Version:**

Ruby-tipped probe with M2 connection thread

Note:

Further styli with other sizes and shank types available on request.

Technical description

Weight	1.97 g
Contact point Ø D	3 mm
Material of shank	Carbide
effective working length	37 mm
Shank Ø S	2 mm
Length L	40 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

Accessories

Stylus extension Length 20 mm	494214 20
-------------------------------	-----------

Stylus cleaning kit	494240
5-way stylus centre M2 Type M2/5	494219 M2/5
Stylus extension Length 40 mm	494214 40
Stylus extension Length 30 mm	494214 30
Stylus extension Length 10 mm	494214 10
Adaptor Type M3/M2	494218 M3/M2