

RENISHAW**Stylus, ruby ball Length 10/11 mm, Contact point Ø D: 8mm****Order data**

Order number	494220 8
GTIN	2050000973444
Item class	49F

Description**Version:**

Ruby-tipped probe with M2 connection thread

Note:

Further styli with other sizes and shank types available on request.

Technical description

Contact point Ø D	8 mm
Shank Ø S	2.5 mm
Weight	1.5 g
Material of shank	Steel
effective working length	11 mm
Length L	11 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

Accessories

5-way stylus centre M2 Type M2/5	494219 M2/5
----------------------------------	-------------

Stylus extension Length 40 mm	494214 40
Stylus extension Length 10 mm	494214 10
Adaptor Type M3/M2	494218 M3/M2
Stylus extension Length 20 mm	494214 20
Stylus extension Length 30 mm	494214 30
Stylus cleaning kit	494240