

## Single test pin Tolerance class 1, Type: 6



### Order data

Order number	483900 6
GTIN	2050001048851
Item class	48A

### Description

#### Version:

Of high quality gauge steel, hardened ( $60 \pm 2$  HRC) and tempered. Surface ground and lapped. From  $\varnothing$  1.5 mm engraved with the size, 0.1 mm – 0.99 mm without a chamfer. From 1.0 mm one end chamfered.

**Tolerance class 1:** Pin  $\varnothing \pm 0.001$  mm.

#### Application:

Degrease before use and grease after use.

#### Note:

When ordering, please additionally state the **desired  $\varnothing$** , e.g. No. 483900 size 5 **10.08** or 483920 size 5 **10.082**.

### Technical description

Gauging pin length	70 mm
Pitch	0.01 mm
Nominal size	12 - 13.99 mm
Calibration	L5
Standard	DIN 2269
Tolerance class	1
Hardness	$60 \pm 2$ HRC
Material	Gauge steel
Type of product	Test pin

## Services

CalibrationTest pin maximum Ø 20	028240 20
DAkkS calibrationTest pin maximum Ø 20	028260 20