

**RENISHAW****Stylus, ruby ball Length 20 mm, Contact point Ø D: 0,5mm**

## Order data

Order number	494222 0,5
GTIN	2050000973451
Item class	49F

## Description

**Version:**

Ruby-tipped probe with M2 connection thread

**Note:**

Further styli with other sizes and shank types available on request.

## Technical description

effective working length	7 mm
Contact point Ø D	0.5 mm
Shank Ø S	0.3 mm
Material of shank	Carbide
Weight	0.5 g
Length L	20 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

## Accessories

5-way stylus centre M2 Type M2/5	494219 M2/5
----------------------------------	-------------

Stylus extension Length 20 mm	494214 20
Stylus extension Length 10 mm	494214 10
Adaptor Type M3/M2	494218 M3/M2
Stylus extension Length 30 mm	494214 30
Stylus cleaning kit	494240
Stylus extension Length 40 mm	494214 40