

**RENISHAW****Stylus, ruby ball Length 40 mm, Contact point Ø D: 5mm****Order data**

Order number	494224 5
GTIN	2050000973512
Item class	49F

**Description****Version:**

Ruby-tipped probe with M2 connection thread

**Note:**

Further styli with other sizes and shank types available on request.

**Technical description**

Contact point Ø D	5 mm
Weight	3.17 g
effective working length	40 mm
Material of shank	Carbide
Shank Ø S	2.5 mm
Length L	40 mm
Connection thread	M2
Material of point	Ruby
Type of product	Probes

**Accessories**

5-way stylus centre M2 Type M2/5	494219 M2/5
----------------------------------	-------------

Adaptor Type M3/M2	494218 M3/M2
Stylus extension Length 40 mm	494214 40
Stylus cleaning kit	494240
Stylus extension Length 20 mm	494214 20
Stylus extension Length 10 mm	494214 10
Stylus extension Length 30 mm	494214 30