

Single test pin Tolerance class 1, Type: 7



Order data

| | |
|--------------|---------------|
| Order number | 483900 7 |
| GTIN | 2050001048868 |
| Item class | 48A |

Description

Version:

Of high quality gauge steel, hardened (60 ± 2 HRC) and tempered. Surface ground and lapped. From \varnothing 1.5 mm engraved with the size, 0.1 mm – 0.99 mm without a chamfer. From 1.0 mm one end chamfered.

Tolerance class 1: Pin $\varnothing \pm 0.001$ mm.

Application:

Degrease before use and grease after use.

Note:

When ordering, please additionally state the **desired \varnothing** , e.g. No. 483900 size 5 **10.08** or 483920 size 5 **10.082**.

Technical description

| | |
|--------------------|----------------|
| Pitch | 0.01 mm |
| Gauging pin length | 70 mm |
| Nominal size | 14 - 15.99 mm |
| Calibration | L5 |
| Standard | DIN 2269 |
| Tolerance class | 1 |
| Hardness | 60 ± 2 HRC |
| Material | Gauge steel |
| Type of product | Test pin |

Services

| | | |
|------------------|-----------------------|-----------|
| DAkS calibration | Test pin maximum Ø 20 | 028260 20 |
| Calibration | Test pin maximum Ø 20 | 028240 20 |