

RENISHAW**Stylus, cylindrical, Cylinder Ø D: 2Rmm****Order data**

Order number	494230 2R
GTIN	2050000973567
Item class	49F

Description**Version:**

Cylindrical ruby contact point with M2 connection thread

Note:

Further probe inserts with other sizes and shank types available on request.

Technical description

effective working length	7.2 mm
Material of shank	ruby
Weight	0.5 g
Cylinder Ø D	2 mm
Length L	20 mm
Connection thread	M2
Type of product	Probes

Accessories

Stylus extension Length 20 mm	494214 20
Adaptor Type M3/M2	494218 M3/M2
Stylus cleaning kit	494240

Stylus extension Length 40 mm	494214 40
Stylus extension Length 30 mm	494214 30
5-way stylus centre M2 Type M2/5	494219 M2/5
Stylus extension Length 10 mm	494214 10