

**Fleece finishing belt (A) SC-BL, 50×2000 mm, Grit equivalent: 180****Order data**

Order number	558506 180
GTIN	4001895726613
Item class	53M

**Description****Version:**

Synthetic nylon non-woven fabric with synthetic resin bonded abrasive grit, long service life, **consistent surface finish, low heat generation.**

Sturdy fleece belt with low belt stretch for very heavy duties.

**Application:**

For rubbing down rough ground or brushed surfaces, for consistent and reproducible results. Also suitable for removing rust film, light soiling, and discolouration.

**Technical description**

Grit designation	medium
Colour	red
Grit equivalent	180
Version	A medium
Series	SC-BL
Grinding medium code	A

Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	50 mm
Linishing belt length	2000 mm
Product name attribute	50×2000 mm
Manufacturer's designation	SC-BL
Type of product	Fleece linishing belt

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions	15-20 m/s	
Steel < 900 N/mm <sup>2</sup>	suitable	10 m/s	P
Steel < 1400 N/mm <sup>2</sup>	suitable	10 m/s	P
Steel < 55 HRC	suitable	10 m/s	H
Steel < 60 HRC	suitable	10 m/s	H
Steel < 67 HRC	suitable	10 m/s	H
INOX	suitable	10 m/s	
Ti	suitable	10 m/s	
GG(G)	suitable	10 m/s	K
CuZn	suitable	10 m/s	N
Plastic, GRP	suitable	10 m/s	
Wood	suitable	10 m/s	
Paint	suitable	10 m/s	
Uni	suitable	10 m/s	
dry	suitable		