

**Fleece finishing belt (A) SC-BL, 100×1000 mm, Grit equivalent: 100****Order data**

| | |
|--------------|---------------|
| Order number | 558510 100 |
| GTIN | 2050001694195 |
| Item class | 53M |

Description**Version:**

Synthetic nylon non-woven fabric with synthetic resin bonded abrasive grit, long service life, **consistent surface finish, low heat generation.**

Sturdy fleece belt with low belt stretch for very heavy duties.

Application:

For rubbing down rough ground or brushed surfaces, for consistent and reproducible results. Also suitable for removing rust film, light soiling, and discolouration.

Technical description

| | |
|----------------------|----------|
| Grit designation | coarse |
| Grit equivalent | 100 |
| Colour | brown |
| Version | A coarse |
| Series | SC-BL |
| Grinding medium code | A |

| | |
|---|-----------------------|
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Linishing belt width | 100 mm |
| Linishing belt length | 1000 mm |
| Product name attribute | 100×1000 mm |
| Manufacturer's designation | SC-BL |
| Type of product | Fleece linishing belt |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | 15-20 m/s | |
| Steel < 900 N/mm ² | suitable | 10 m/s | P |
| Steel < 1400 N/mm ² | suitable | 10 m/s | P |
| Steel < 55 HRC | suitable | 10 m/s | H |
| Steel < 60 HRC | suitable | 10 m/s | H |
| Steel < 67 HRC | suitable | 10 m/s | H |
| INOX | suitable | 10 m/s | |
| Ti | suitable | 10 m/s | |
| GG(G) | suitable | 10 m/s | K |
| CuZn | suitable | 10 m/s | N |
| Plastic, GRP | suitable | 10 m/s | |
| Wood | suitable | 10 m/s | |
| Paint | suitable | 10 m/s | |
| Uni | suitable | 10 m/s | |
| dry | suitable | | |