


**VALTITAN precision needle file Overall length 180 mm, SC 0 / GC 1, Type: 5**

**Order data**

Order number	527550 5
GTIN	613548045657
Item class	53B

**Description**
**Version:**

**High performance needle files** with extremely high wear resistance. Surface hardness **1200 HV**. The special tooth profile prevents files clogging, files can be easily cleaned by gentle tapping (on wood).

**Standard:**

**SH = Schweizer Hieb; DH = Deutscher Hieb.**

**Technical description**

File surfaces	4
Cross section	2.6×2.6 mm
Shape description	square
Overall length	180 mm
Swiss cut	0
equivalent to German cut	1
Product name attribute	SC 0 / GC 1
incl. file handle	no
Type of product	Precision needle file

**User data**

	Suitability	V <sub>c</sub>	ISO code
--	-------------	----------------	----------

Alu Mg	suitable
Steel < 900 N/mm <sup>2</sup>	suitable
Steel < 1400 N/mm <sup>2</sup>	suitable
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable
Steel < 67 HRC	suitable
INOX	suitable
Ti	suitable
GG(G)	suitable
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable
Uni	suitable

---

## Accessories

Quick-release handlefor needle files Type 3	519700 3
Quick-release handlefor needle files Type 2	519700 2