

**Single test pin Tolerance class 2, Type: 4****Order data**

Order number	483941 4
GTIN	2050001056979
Item class	48A

**Description****Version:**

Test pins of alloyed tool steel  $60 \pm 2$  HRC. Pin: Hardened, tempered, ground, and lapped. Handle:  $\emptyset$  value engraved.

**Note:**

When ordering, please **additionally state the desired  $\emptyset$** , e.g. No. 483940 size 2 **0.35**.

**Technical description**

Pitch	0.01 mm
Overall length	83 mm
Test length	63 mm
Nominal size	1 - 2.99 mm
Calibration	L5
Standard	DIN 2269
Tolerance class	2
Hardness	$60 \pm 2$ HRC
Material	alloyed tool steel
Type of product	Test pin

**Services**

DAkkS calibration	Test pin maximum $\emptyset$ 20	028260 20
		028240 20

CalibrationTest pin maximum Ø 20

---