

**Precision needle file Overall length 160 mm, SC 2 / GC 3, Type: 5****Order data**

Order number	527340 5
GTIN	613548047989
Item class	53B

**Description****Version:**

Swiss precision needle files satisfy the highest demands for accuracy of shape, precision cut, removal rate and tool life. Cut length =  $\frac{1}{2}$  file length. Manufactured from special steel for precision files with high wear resistance (65-66 HRC). Precisely determined shapes, special cut angle and large selection of different cuts. High metal removal rate.

**Quick-release handle see No. 519700.**

**Standard:**

**SH = Schweizer Hieb; DH = Deutscher Hieb.**

**Note:**

See also Habilis precision files No. 527050 – 527070.

**Technical description**

File surfaces	4
Overall length	160 mm
Cross section	2.4×2.4 mm
Shape description	square

Swiss cut	2
equivalent to German cut	4
Product name attribute	SC 2 / GC 3
Type of product	Precision needle file

## User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Uni	suitable only under restricted conditions		

## Accessories

Quick-release handle for needle files Type 2	519700 2
Quick-release handle for needle files Type 3	519700 3