



VALTITAN precision needle file Set 6 pieces, Overall length mm / Swiss cut: 180/0



Order data

Order number	527660 180/0
GTIN	613548045770
Item class	53B

Description

Version:

High performance needle files with extremely high wear resistance. Surface hardness **1200 HV**. The special tooth profile prevents files clogging, files can be easily cleaned by gentle tapping (on wood).

Standard:

SH = Schweizer Hieb; DH = Deutscher Hieb.

Supplied with:

In a plastic wallet. 1 each file form flat plain, half-round, round, square, 3-square and barette.

Technical description

Overall length	180 mm
Swiss cut	0
Type of product	Precision needle file

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		

Steel < 1400 N/mm ²	suitable
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable
Steel < 67 HRC	suitable
INOX	suitable
Ti	suitable
GG(G)	suitable
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable
Uni	suitable

Accessories

Quick-release handle for needle files Type 3	519700 3
Quick-release handle for needle files Type 2	519700 2