

Hone – original Arkansas (white), grit 8000, square, Length×Width: 100X13mm



Order data

| | |
|--------------|---------------|
| Order number | 558720 100X13 |
| GTIN | 4037073002149 |
| Item class | 56Z |

Description

Version:

Natural stone (original-Arkansas) of very fine grit quartzite; very strong edges. For the finest surfaces and burr-free grinding. Grit 5000 (pre-grinding), grit 8000 (polishing).

Application:

For **deburring, sharpening, truing** and **chamfering** of tools and tool cutters. For re-working bores, surfaces and edges in mould making. Also for improving the surface for stock removal, finishing, and polishing. **Best used with oil, paraffin or water.**

Note:

Low dose of oil increases tool life and edge sharpness.

Technical description

| | |
|------------------|--------------------|
| Grit | 8000 |
| Length | 100 mm |
| Grit designation | Polishing |
| Width | 13 mm |
| Colour | white |
| Grinding media | Arkansas quartzite |
| Shape | square |
| Type of product | Hone |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|---|----------------------|-----------------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| Carbide (HM) | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable only under restricted conditions | | |
| Plastic, GRP | suitable only under restricted conditions | | |
| Uni | suitable | | |
| wet maximum | suitable | | |
| dry | suitable only under restricted conditions | | |