



Precision riffler file fine Length 150 mm, SC 2 / GC 2, Type: 914



Order data

Order number	528050 914
GTIN	613548078105
Item class	53B

Description

Version:

The blanks for the **Swiss precision riffler files** are forged from special steel and ground; precision machines give them an extremely precise cut of even density and depth with a hardness of **65 – 66 HRC**. The quality of these riffler files is provided by a clean and precise cut to the very tip of the point. These files feature a very high shape accuracy and a high metal removal rate with extremely long tool life.

Application:

For precise and delicate work even on very hard materials, e.g. in mould and tool making.

Technical description

Cross section	3.4×1.5 mm
Grit designation	fine
Swiss cut	2
equivalent to German cut	2
Cut	38 cm
Overall length	150 mm
Product name attribute	SC 2 / GC 2
Type of product	Precision riffler file

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Uni	suitable only under restricted conditions		