



## Nut spinner set fully insulated, Number of keys: 5



### Order data

Order number	622510 5
GTIN	4010995228200
Item class	63K

### Description

#### Version:

Handle and blade **fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 0682-201**. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage. **Application:** For use at voltages up to 1000 V.

Ergonomic multi-component handle with non-roll flats. **Blade** of chrome vanadium steel, burnished. Long design, deep hexagon nut spinner head for projecting threads.

#### Standard:

**DIN 3125**

#### Material:

**Ergonomic multi-component handle** with non-roll flats, **Blade** of chrome vanadium steel, burnished, fully insulated.

#### Content:

1 pc. each No. 622500: 7; 8; 9; 10; 13 mm

### Technical description

Number of keys	5
Manufacturer's designation	SoftFinish® electric
Standard	DIN 3125
Standard	DIN EN IEC 60900 / VDE 0682-201
Drive profile	Hexagon socket

Type of product	Socket spanner
-----------------	----------------

---

## Accessories

Nut spinner with handlefully insulated Width across flats 9 mm	622500 9
--	----------

Nut spinner with handlefully insulated Width across flats 13 mm	622500 13
---	-----------

Nut spinner with handlefully insulated Width across flats 7 mm	622500 7
--	----------

Nut spinner with handlefully insulated Width across flats 8 mm	622500 8
--	----------

Nut spinner with handlefully insulated Width across flats 10 mm	622500 10
---	-----------