



Nut spinner set fully insulated, Number of keys: 11



Order data

Order number	622510 11
GTIN	4010995228217
Item class	63K

Description

Version:

Handle and blade **fully insulated up to 1000 V to DIN EN IEC 60900 / VDE 0682-201**. Each of these screwdrivers is individually tested in a water bath for insulation breakdown under high voltage. **Application:** For use at voltages up to 1000 V.

Ergonomic multi-component handle with non-roll flats. **Blade** of chrome vanadium steel, burnished. Long design, deep hexagon nut spinner head for projecting threads.

Standard:

DIN 3125

Material:

Ergonomic multi-component handle with non-roll flats, **Blade** of chrome vanadium steel, burnished, fully insulated.

Content:

1 pc. each No. 622500: Size 5.5; 6; 7; 8; 9; 10; 11; 13; 14; 16; 17

Technical description

Number of keys	11
Manufacturer's designation	SoftFinish® electric

Standard	DIN 3125
Standard	DIN EN IEC 60900 / VDE 0682-201
Drive profile	Hexagon socket
Type of product	Socket spanner

Accessories

Nut spinner with handlefully insulated Width across flats 11 mm	622500 11
Nut spinner with handlefully insulated Width across flats 13 mm	622500 13
Nut spinner with handlefully insulated Width across flats 8 mm	622500 8
Nut spinner with handlefully insulated Width across flats 5,5 mm	622500 5,5
Nut spinner with handlefully insulated Width across flats 7 mm	622500 7
Nut spinner with handlefully insulated Width across flats 17 mm	622500 17
Nut spinner with handlefully insulated Width across flats 6 mm	622500 6
Nut spinner with handlefully insulated Width across flats 9 mm	622500 9
Nut spinner with handlefully insulated Width across flats 10 mm	622500 10