

**IMPACT socket 3/8 inch, for Torx® screws, Torx® profile: E12****Order data**

| | |
|--------------|---------------|
| Order number | 650500 E12 |
| GTIN | 4045197214799 |
| Item class | 62D |

Description**Version:**

Sturdy shape especially for use with electric or compressed air impact wrenches. With cross hole and snap ring groove for securing sockets. Internal square to DIN 3121.

For safety reasons must always be secured using a suitable locking pin and O-ring.

Material:

Chrome molybdenum steel, surface burnished.

Technical description

| | |
|--------------------------|-------------------------|
| Profile size A | 11.7 mm |
| Torx® profile | E12 |
| Length | 32 mm |
| Ø drive output end | 15 mm |
| Square drive | 3/8 in |
| Drive profile | Socket for TORX® screws |
| suitable for machine use | yes |
| Type of product | Socket insert |

Accessories

| | |
|---|---------------|
| Locking pin for bits and sockets, 3/8 inch Ø×Length 2,5X14 mm | 650900 2,5X14 |
| Extractor for retainer clips | 650785 |
| "O" ring for bits and sockets, 3/8 inch Ø 18 mm | 650800 18 |
| Retainer clip set for bits and sockets, 3/8 inch, including extractor, 10 pieces Type 1 | 650790 1 |