



Swivel end socket spanner set, Number of keys: 7



Order data

Order number	622810 7
GTIN	8014230038681
Item class	63P

Description

Version:

The slideable T-handle is fitted with an end-stop to ensure it does not slide out.

With swivel jointed head (torsion drive 50°, swing drive up to 90°). The swivel angle is secured by an integral spring.

Material:

Chrome vanadium steel, chrome-plated.

Content:

1 each socket spanner No. 622800: Size 8; 10; 11; 13; 14; 17; 19

Technical description

Number of keys	7
Rotation angle	50 degrees
Working angle	90 degrees
Drive profile	Hexagon socket
Material	Chrome vanadium steel
Surface	chrome-plated
Type of product	Socket spanner

Accessories

Swivel end socket spanner Width across flats 11 mm	622800 11
Swivel end socket spanner Width across flats 19 mm	622800 19
Swivel end socket spanner Width across flats 8 mm	622800 8
Swivel end socket spanner Width across flats 13 mm	622800 13
Swivel end socket spanner Width across flats 14 mm	622800 14
Swivel end socket spanner Width across flats 17 mm	622800 17
Swivel end socket spanner Width across flats 10 mm	622800 10